

Optic Magnifier

Public Sewing Announcement

elna
SWISS DESIGN


When you need to get a closer view, attach the Optic Magnifier to make it easy to see the tiniest detail under the needle. Useful when threading, adjusting the position of the fabric and carrying out detailed work.

Full Set Including Holder and 20x, 40x, and 60x Magnifications

Part Number: 202130002


NEW Set Including Only Holder and 20x Magnification

Part Number: 202399001



To attach the Optic Magnifier

1. Locate a small hole on the bottom left side of the machine head with your hand.
2. Insert the metal post on the back of the Optic Magnifier. Push until you feel it catch.
3. Remove by pulling down on the metal post.



To switch the Optic Magnifiers

1. Optic Magnifier set 202130002 comes with three levels of magnifications – 20x, 40x, and 60x.
2. To change the magnifiers, flip the plastic spring loaded switch to the left of the magnifier. This will loosen the spring holding the magnifier in place.
3. Put the desired magnification in place, and flip the plastic switch back to engage the spring.



Compatible with:

eXpressive 920
eXpressive 900
eXcellence 780
eXcellence 760 PRO
eXcellence 730 PRO
eXcellence 720 Pro

eXpressive 860
eXcellence 680

eXperience 570
eXperience 560
Lotus 2

it's
elna
smooth
elnaUSA.com